EVERLIGHT EVERLIGHT ELECTRONICS CO., LTD.

Technical Data Sheet

Infrared Remote-control Receiver Module

Features

- High shielding against electric field disturbance.
- Circular lens to improve the receive characteristic.
- Line-up for various center carrier frequencies.
- Low voltage and low power consumption.
- High immunity against ambient light.
- Photodiode with integrated circuit.
- TTL and CMOS compatibility.
- Top-received SMD.
- Suitable burst length ≥ 10 pulses/burst.
- This product itself will remain within RoHS compliant version.
- Pb free.
- External dimensions 5.3(L)*2.9(W)*3.65(H)mm.

Descriptions

The device is a miniature SMD type infrared remote control system receiver that has been developed and designed by utilizing the most updated IC technology. The PIN diode and preamplifier are assembled on PCB, the epoxy package is designed as an IR filter. The demodulated output signal can directly be decoded by a microprocessor.

Applications

- 1. Light detecting portion of remote control
- AV instruments such as Audio, TV, VCR, CD, MD, etc.
- Home appliances such as Air-conditioner, Fan, etc.
- The other equipments with wireless remote control.
- CATV set top boxes
- Multi-media Equipment

Device Selection Guide

PART	MATERIAL	COLOR
Chip	Silicon	
Package	Ероху	Black
Metal case	SPCC	Silver white

<u>IRM-H538/TR2</u>






http://www.everlight.com Prepared date : 11-24-2006 Rev 1 Page: 1 of 12 Prepared by : Cindy Lin EVERLIGHT E

EVERLIGHT ELECTRONICS CO., LTD.

IRM-H538/TR2

Package Dimensions




Notes: 1.All dimensions are in millimeters.

2.Tolerances unless dimensions ±0.2mm.

Soldering patterns

The following soldering patterns are recommended for reflow-soldering :



Available Types For Different Carrier Frequencies

IRM_H538/TR2 38 kHz	Туре	Carrier Frequencies (Typ)
IKW-11550/1K2 50 KHZ	IRM-H538/TR2	38 kHz

Everlight Electronics Co., Ltd. Device No: DMO-538-400 http://www.everlight.com Prepared date : 11-24-2006 Rev 1 Page: 2 of 12 Prepared by : Cindy Lin

IRM-H538/TR2

Absolute Maximum Ratings (Ta=25°C)

EVERLIGHT

Parameter	Symbol	Symbol Rating		Notice
Supply Voltage	Vcc	0~6	V	
Operating Temperature	Topr	-25 ~ +85	°C	
Storage Temperature	Tstg	-40 ~ +85	°C	

Recommended Operating Condition

Supply Voltage Rating: Vcc 2.7V to 5.5V

Electro-Optical Characteristics (Ta=25°C, and Vcc=3.0V)

Parameter	Symbol	MIN.	ТҮР.	MAX.	Unit	Condition
Supply Current	Icc			1.2	mA	No signal input
Peak Wavelength	λp		940		nm	
Reception Distance	L ₀	8			m	
	L ₄₅	5				
Half Angle(Horizontal)	Θ_h		45		deg	At the ray axis *1
Half Angle(Vertical)	Θ_{v}		45		deg	
High Level Pulse Width	$T_{\rm H}$	400		800	μ s	At the ray axis
Low Level Pulse Width	T_L	400		800	μ s	*2
High Level Output Voltage	V_{H}	2.7			V	
Low Level Output Voltage	V_L		0.2	0.5	V	

Notes:

*1: The ray receiving surface at a vertex and relation to the ray axis in the range of $\theta = 0^{\circ}$ and $\theta = 45^{\circ}$.

*2 : A range from 30cm to the arrival distance. Average value of 50 pulses.

IRM-H538/TR2

The Notice of Application:

EVERLIGHT

Transmission remote control signal consist of four parts: Encode Part, IR Transmitter Source, IRM device, Decode Part

- 1. When IRM-H538 code select frequency, it need to well understand the center system of encode part.
- 2. Strong or weak light of IR Transmitter can affect distance of transmission.
- 3. Minimum Burst Length Tburst (number of pulses per burst) : 10 cycles
- 4. It needs to ensure the translation range of decode part if it is applied to the pulse-width range.

If the above items hardly assure of its application, it'll cause NG(no good) message from the edge of signal.

Test Method :

The specified electro-optical characteristics is satisfied under the following

Conditions at the controllable distance.

①Measurement place

A place that is nothing of extreme light reflected in the room.

②External light

Project the light of ordinary white fluorescent lamps which are not high Frequency lamps and must be less then 10 Lux at the module surface.

 $(Ee \leq 10Lux)$

3Standard transmitter

A transmitter whose output is so adjusted as to **Vo=400mVp-p** and the output Wave form shown in Fig.-1.According to the measurement method shown in Fig.-2 the standard transmitter is specified.


However, the infrared photodiode to be used for the transmitter should be

 $\lambda p=940nm, \Delta \lambda = 50nm$. Also, photodiode is used of PD438B(Vr=5V).


(Standard light / Light source temperature 2856°K).

Measuring system

According to the measuring system shown in Fig.-3



D.U.T output Pulse



Everlight Electronics Co., Ltd. Device No: DMO-538-400

http://www.everlight.com Prepared date : 11-24-2006 Rev 1 Page: 4 of 12 Prepared by : Cindy Lin

IRM-H538/TR2





Fig.-2 Measuring Method

EVERLIGHT

Application Circuit :



RC Filter should be connected closely between Vcc pin and GND pin.

Everlight Electronics Co., Ltd. Device No: DMO-538-400

http://www.everlight.com Prepared date : 11-24-2006


IRM-H538/TR2

Typical Electro-Optical Characteristics Curves

Fig.-4 Relative Spectral Sensitivity vs.

Wavelength

EVERLIGHT



Direction






Fig.-6 Output Pulse Length vs. Arrival Distance Fig.-7 Arrival Distance vs. Supply Voltage





Everlight Electronics Co., Ltd. Device No: DMO-538-400

http:\\www.everlight.com Prepared date : 11-24-2006 Rev 1 Page: 6 of 12 Prepared by : Cindy Lin

IRM-H538/TR2


Typical Electro-Optical Characteristics Curves


Fig.-8 Relative Transmission Distance

EVERLIGHT

vs. Center Carrier Frequency

Fig.-9 Arrival Distance vs. Ambient Temperature





http://www.everlight.com Prepared date : 11-24-2006 Rev 1 Page: 7 of 12 Prepared by : Cindy Lin

IRM-H538/TR2

Reliability Test Item And Condition

EVERLIGHT

The reliability of products shall be satisfied with items listed below. Confidence level : 90% LTPD : 10%

Reflow Terms: JEDEC Level 4 Specification

Drying; Temp.:125°C 24hrs \rightarrow Moisture 30°C / 60% RH 96hrs \rightarrow Reflow Temp.: 260°C±5°C 10sec, 3 times

Note:

1. Not sooner than 15 minutes and not longer than 4 hours after removal from the temperature/humidity chamber.

2. The time between reflow shall be 5 minutes minimum and 60 minutes maximum.

Test Items	Test Conditions	Failure Judgement Criteria	Samples(n) Defective(c)
Temperature cycle	1 cycle : $-25^{\circ}C \iff +85^{\circ}C$ (30min)(5min)(30min) 300 cycle test	$L_0 \leq L \times 0.8$ $L_{45} \leq L \times 0.8$	n=76,c=0
High temperature test	Temp : +85℃ Vcc : 5V 1000hrs	L: Lower specification limit	n=76,c=0
Low temperature storage	Temp:-40°C 1000hrs	*Icc : Operate Current (mA) Variation≦±20%:	n=76,c=0
High temperature High humidity	Ta:85°C ,RH:85% 1000hrs		n=76,c=0

Everlight Electronics Co., Ltd. Device No: DMO-538-400 http://www.everlight.com Prepared date : 11-24-2006 Rev 1 Page: 8 of 12 Prepared by : Cindy Lin EVERLIGHT EVERLIGHT ELECTRONICS CO., LTD.

<u>IRM-H538/TR2</u>

Recommended method of storage

Dry box storage is recommended as soon as the aluminum bag has been opened prevent moisture absorption. The following conditions should be observed, if dry boxes are not available:

• Storage temperature 10° C to 30° C

• Storage humidity $\leq 60\%$ RH max.

After more than 72 hours under these conditions moisture content will be too high for Reflow soldering:


In case of moisture absorption, the devices will recover to former condition by drying under the following condition:

192 hours at $40^{\circ}C + 5^{\circ}C / -0^{\circ}C$ and 5%RH (dry air / nitrogen) or 96 hours at $60^{\circ}C + 5^{\circ}C$ and < 5%RH for all device containers or 24 hours at $125^{\circ}C + 5^{\circ}C$ not suitable for reel or tubes.

ESD Precaution

Proper storage and handing procedures should be followed to prevent ESD damage to the devices especially when they are removed from the Anti-static bag. Electro-Static Sensitive Devices warning labels are on the packing.

Recommended Solder Profile



Notice:

- (1) Reflow soldering should not be done more than two times.
- (2) When soldering, do not put stress on the IRM-H538/TR1 Series devices during heating.
- (3) After soldering, do not warp the circuit board.

IRM-H538/TR2


Soldering Iron

EVERLIGHT

Each terminal is to go to the tip of soldering iron temperature less than 350° C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

Repairing

Repair should not be done after the Devices have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the Devices will or will not be damaged by repairing.






Packing Quantity Specification


1. 2000 PCS/1 Reel

2. 5 Reel /1Carton

Carrier Tape Dimensions: Loaded quantity 2000 PCS per reel



Packing process



Everlight Electronics Co., Ltd. Device No: DMO-538-400


http://www.everlight.com Prepared date : 11-24-2006 Rev 1 Page: 11 of 12 Prepared by : Cindy Lin

IRM-H538/TR2

EVERLIGHT EVERLIGHT ELECTRONICS CO.,LTD.

IRM-H538/TR2

Label Form Specification



CPN: Customer's Production Number P/N : Production Number QTY: Packing Quantity CAT: None HUE: None REF: Reference LOT No: Lot Number MADE IN TAIWAN: Production Place

Notes

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 3. These specification sheets include materials protected under copyright of EVERLIGHT corporation. Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.

EVERLIGHT ELECTRONICS CO., LTD. Office: No 25, Lane 76, Sec 3, Chung Yang Rd, Tucheng, Taipei 236, Taiwan, R.O.C *Tel:* 886-2-2267-2000, 2267-9936 *Fax:* 886-2267-6244, 2267-6189, 2267-6306 *http:*\\www.everlight.com

Everlight Electronics Co., Ltd. Device No: DMO-538-400 http://www.everlight.com Prepared date : 11-24-2006 Rev 1 Page: 12 of 12 Prepared by : Cindy Lin