查询XB1006-BD供应商

High Dynamic Range/Positive Gain Slope
Excellent LO Driver/Buffer Amplifier
Low Noise or Power Bias Configurations

X 3.2 dB Noise Figure at Low Noise Bias

× 100% Visual Inspection to MIL-STD-883

× +15 dBm P1dB Compression Point at Power Bias × 100% On-Wafer RF, DC and Noise Figure Testing

Mimix Broadband's three stage 18.0-38.0 GHz GaAs

MMIC buffer amplifier has a small signal gain of 21.0 dB with a positive gain slope, and a noise figure of 3.2 dB across the band. This MMIC uses Mimix Broadband's 0.15 µm GaAs PHEMT device model technology, and is based upon electron beam lithography to ensure high repeatability and uniformity. The chip has surface passivation to protect and provide a rugged part with backside via holes and gold metallization to allow either a conductive epoxy or eutectic solder die attach

process. This device is well suited for Millimeter-wave

Point-to-Point Radio, LMDS, SATCOM and VSAT

捷多邦,专业PCB打样工厂,24小时加急出货

18.0-38.0 GHz GaAs MMIC Buffer Amplifier

February 2008 - Rev 25-Feb-08

🗙 21.0 dB Small Signal Gain

General Description

Method 2010

applications.

Features

XB1006-BD

Chip Device Layout

Absolute Maximum Ratings

+6.0 VDC
120 mA
+0.3 VDC
+5 dBm
-65 to +165 ⁰ C
-55 to MTTF Table ⁵
MTTF Table ⁵

(5) Channel temperature affects a device's MTBF. It is recommended to keep channel temperature as low as possible for maximum life.

Electrical Characteristics (Ambient Temperature T = 25 °C)

Units	Min.	Тур.	Max.
GHz	18.0	-	38.0
dB	4.0	14.0	-
dB	7.0	12.0	- 17
dB	19.0	21.0	27.0
dB		+/-2.0	0250
dB	40.0	50.0	-
dB	1	3.2	4.5
dBm	-	+15.0	-
dBm	-	+25.0	-
dBm	+14.0	+18.0	-
VDC	-	+3.5	+5.5
VDC	-1.2	-0.3	+0.1
mA	-	50	100
	GHz dB dB dB dB dB dB dBm dBm dBm dBm VDC VDC	GHz 18.0 dB 4.0 dB 7.0 dB 19.0 dB - dB 40.0 dB - dB 40.0 dB - VDC - VDC -1.2	GHz 18.0 - dB 4.0 14.0 dB 7.0 12.0 dB 19.0 21.0 dB - +/-2.0 dB 40.0 50.0 dB - 3.2 dBm - +15.0 dBm - +25.0 dBm +14.0 +18.0 VDC - +3.5 VDC -1.2 -0.3

(1) Optional low noise bias Vd1,2=3.5V, Id=50mA will typically yield 3-4dB decreased P1dB and OIP3.

(2) Measured using constant current.

(3) Unless otherwise indicated, min/max over 18.0-38.0 GHz and biased at Vd=5.5V, Id1=50mA, Id2=50mA.


(4) Unless otherwise indicated, min/max over 20.0-38.0 GHz and biased at Vd=3.5V, Id1=25mA, Id2=25mA.


Mimix Broadband, Inc., 10795 Rockley Rd., Houston, Texas 77099 Tel: 281.988.4600 Fax: 281.988.4615 mimixbroadband.com Page 1 of 11


February 2008 - Rev 25-Feb-08



Buffer Amplifier Measurements








Mimix Broadband, Inc., 10795 Rockley Rd., Houston, Texas 77099 Tel: 281.988.4600 Fax: 281.988.4615 mimixbroadband.com Page 2 of 11





Buffer Amplifier Measurements (cont.)





Page 3 of 11




February 2008 - Rev 25-Feb-08

Buffer Amplifier Measurements (cont.)









Mimix Broadband, Inc., 10795 Rockley Rd., Houston, Texas 77099 Tel: 281.988.4600 Fax: 281.988.4615 mimixbroadband.com Page 4 of 11


February 2008 - Rev 25-Feb-08




Buffer Amplifier Measurements (cont.)









Mimix Broadband, Inc., 10795 Rockley Rd., Houston, Texas 77099 Tel: 281.988.4600 Fax: 281.988.4615 mimixbroadband.com Page 5 of 11

February 2008 - Rev 25-Feb-08

S-Parameters

Typical S-Parameter Data for XB1006-BD Vd=3.5 V, Id1=25 mA, Id2=25 mA

Frequency (GHz)	S11 Mag dB	S11 Phase Ang ^o	S12 Mag dB	S12 Phase Ang ^o	S21 Mag dB	S21 Phase Ang ^o	S22 Mag dB	S22 Phase Ang ^o
0.50000	-0.01	-0.29	-78.68	8.90	-77.37	-176.19	-0.02	-2.04
1.24250	-0.02	-5.97	-55.36	-27.84	-97.96	-18.44	-0.22	-36.80
1.98500	-0.05	-11.39	-47.08	131.76	-99.03	10.31	-1.13	-70.98
2.72750	-0.06	-16.82	-33.88	23.33	-90.81	-69.68	-4.42	-97.96
3.47000	-0.06	-22.34	-34.52	-78.78	-86.32	62.90	-4.06	-86.96
4.21250	-0.07	-27.94	-41.53	-128.85	-82.39	12.94	-1.73	-108.69
4.95500	-0.08	-33.66	-50.48	-131.07	-73.36	-32.06	-1.31	-131.13
5.69750	-0.08	-39.53	-57.08	-85.12	-73.18	-28.90	-1.37	-149.61
6.44000	-0.10	-45.53	-58.91	-23.44	-71.12	-52.31	-1.56	-165.64
7.18250	-0.11	-51.65	-50.90	73.26	-68.50	-52.25	-1.80	179.86
7.92500	-0.13	-58.15	-38.14	90.65	-68.92	-59.64	-2.07	166.35
8.66750	-0.15	-64.83	-28.68	83.41	-63.09	-58.13	-2.38	153.33
9.41000	-0.18	-71.83	-20.83	68.82	-59.82	-74.90	-2.71	140.43
10.15300	-0.22	-79.27	-14.04	49.43	-58.10	-93.36	-3.11	127.22
10.89500	-0.26	-87.16	-8.04	26.33	-56.47	-111.16	-3.61	113.42
11.63700	-0.32	-95.68	-2.71	0.09	-56.05	-117.90	-4.32	98.77
12.38000	-0.40	-105.00	1.96	-28.91	-55.15	-134.10	-5.32	83.34
13.12300	-0.51	-115.16	5.95	-59.68	-53.23	-142.49	-6.76	67.76
13.86500	-0.68	-126.77	9.27	-91.70	-52.12	-157.28	-8.66	53.13
14.60800	-0.99	-140.05	11.96	-123.78	-51.94	-174.08	-10.98	41.18
15.35000	-1.45	-154.85	14.17	-155.15	-51.66	178.20	-13.48	32.59
16.09300	-2.19	-171.62	16.00	174.27	-52.01	157.70	-15.68	27.86
16.83500	-3.18	169.23	17.58	144.27	-53.65	160.00	-17.38	22.98
17.57800	-4.70	147.05	18.82	114.12	-52.78	154.41	-18.61	18.88
18.32000	-6.78	121.63	19.67	84.88	-53.35	146.89	-19.09	11.20
19.06300	-9.56	93.00	20.28	57.17	-52.52	145.73	-18.76	-4.30
19.80500	-12.54	59.48	20.75	30.12	-53.50	144.77	-18.80	-22.95
20.54700	-15.22	20.64	20.98	4.36	-52.49	140.88	-18.73	-42.86
21.29000	-16.54	-19.05	21.11	-19.88	-51.43	138.82	-18.36	-61.50
22.03200	-17.11	-54.31	21.20	-43.04	-50.69	129.44	-17.87	-78.95
22.77500	-17.55	-79.68	21.29	-65.10	-50.48	124.99	-16.93	-92.61
23.51700	-18.58	-102.87	21.42	-86.84	-49.25	123.36	-16.02	-108.44
24.26000	-21.05	-120.90	21.49	-108.11	-48.36	107.54	-15.57	-121.50
25.00300	-25.97	-127.59	21.55	-128.72	-47.55	93.53	-15.23	-132.33
25.74500	-29.89	-94.55	21.73	-148.87	-49.21	79.52	-14.52	-141.30
26.48800	-27.51	-57.28	21.94	-169.44	-49.14	67.70	-13.99	-150.67

Mimix Broadband, Inc., 10795 Rockley Rd., Houston, Texas 77099 Tel: 281.988.4600 Fax: 281.988.4615 mimixbroadband.com Page 6 of 11

February 2008 - Rev 25-Feb-08



S-Parameters (cont.)


Typical S-Parameter Data for XB1006-BD Vd=3.5 V, Id1=25 mA, Id2=25 mA

Frequency (GHz)	S11 Mag dB	S11 Phase Ang⁰	S12 Mag dB	S12 Phase Ang⁰	S21 Mag dB	S21 Phase Ang⁰	S22 Mag dB	S22 Phase Ang ^o
27.23000	-23.18	-58.03	22.04	169.35	-51.07	54.80	-13.51	-163.64
27.97300	-20.24	-57.14	22.17	149.03	-52.87	47.91	-13.50	-174.19
28.71500	-17.68	-70.31	22.34	128.56	-53.75	29.22	-13.55	176.51
29.45800	-15.93	-85.00	22.49	107.61	-57.28	7.05	-13.69	166.23
30.20000	-14.78	-98.59	22.63	86.72	-62.67	-31.77	-14.33	154.91
30.94200	-13.90	-114.29	22.78	65.37	-61.11	-92.67	-14.82	145.28
31.68500	-12.79	-130.42	23.03	43.74	-57.27	-144.70	-16.38	135.57
32.42800	-11.58	-148.09	23.28	20.80	-50.81	-169.03	-17.81	133.09
33.17000	-10.38	-169.13	23.39	-4.06	-50.09	155.22	-17.54	133.68
33.91300	-9.61	168.38	23.26	-28.70	-49.02	141.03	-17.39	126.24
34.65500	-9.24	150.01	23.18	-53.03	-47.85	148.60	-17.39	122.78
35.39800	-8.53	131.44	22.99	-77.65	-46.07	123.72	-14.80	110.38
36.14000	-8.26	114.42	23.21	-102.42	-45.46	109.96	-12.72	88.54
36.88300	-7.66	101.05	23.65	-133.11	-45.22	102.42	-10.07	66.35
37.62500	-7.09	90.20	23.83	-171.52	-43.57	80.60	-6.86	33.29
38.36800	-5.94	78.00	22.32	143.51	-43.98	58.51	-4.77	-4.19
39.11000	-4.96	63.52	18.86	102.53	-47.57	24.79	-4.42	-38.32
39.85200	-4.73	50.11	14.56	69.36	-50.77	46.25	-4.69	-64.56
40.59500	-4.49	39.33	9.90	43.68	-54.23	74.76	-5.28	-82.81
41.33700	-4.38	30.28	5.25	23.02	-51.35	68.33	-5.75	-95.66
42.08000	-4.10	21.30	0.58	6.42	-45.02	53.96	-5.91	-104.65
42.82200	-3.84	14.19	-4.39	-5.56	-46.84	40.42	-6.02	-112.58
43.56500	-3.84	6.00	-9.71	-11.55	-43.78	-0.02	-5.92	-119.63
44.30700	-3.61	-1.31	-15.12	-0.23	-45.30	-10.20	-5.66	-124.45
45.05000	-3.44	-8.97	-17.19	21.22	-49.42	-27.63	-5.65	-130.14

Mimix Broadband, Inc., 10795 Rockley Rd., Houston, Texas 77099 Tel: 281.988.4600 Fax: 281.988.4615 mimixbroadband.com



February 2008 - Rev 25-Feb-08




(Note: Engineering designator is 28LN3UA0102)

Units: millimeters (inches) Bond pad dimensions are shown to center of bond pad. Thickness: 0.110 +/- 0.010 (0.0043 +/- 0.0004), Backside is ground, Bond Pad/Backside Metallization: Gold All DC Bond Pads are 0.100 x 0.100 (0.004 x 0.004). All RF Bond Pads are 0.100 x 0.200 (0.004 x 0.008) Bond pad centers are approximately 0.109 (0.004) from the edge of the chip. Dicing tolerance: +/- 0.005 (+/- 0.0002). Approximate weight: 1.612 mg. Bond Pad #1 (RF In) Bond Pad #3 (Vd2) Bond Pad #5 (Vg2)

Bond Pad #4 (RF Out)

Bond Pad #6 (Vg1)

Bias Arrangement



Bond Pad #2 (Vd1)

Mimix Broadband, Inc., 10795 Rockley Rd., Houston, Texas 77099 Tel: 281.988.4600 Fax: 281.988.4615 mimixbroadband.com Page 8 of 11

February 2008 - Rev 25-Feb-08

BROADBANDM X B1006-BD

App Note [1] Biasing - As shown in the bonding diagram, this device can be operated with all three stages in parallel, and can be biased for low noise performance or high power performance. Low noise bias is nominally Vd=3.5V, Id=50mA. More controlled performance will be obtained by separately biasing Vd1 and Vd2 each at 3.5V, 25mA. Power bias may be as high as Vd=5.5V, Id=100mA with all stages in parallel, or most controlled performance will be obtained by separately biasing Vd1 and Vd2 each at 5.5V, 50mA. It is also recommended to use active biasing to keep the currents constant as the RF power and temperature vary; this gives the most reproducible results. Depending on the supply voltage available and the power dissipation constraints, the bias circuit may be a single transistor or a low power operational amplifier, with a low value resistor in series with the drain supply used to sense the current. The gate of the pHEMT is controlled to maintain correct drain current and thus drain voltage. The typical gate voltage needed to do this is -0.3V. Typically the gate is protected with Silicon diodes to limit the applied voltage. Also, make sure to sequence the applied voltage to ensure negative gate bias is available before applying the positive drain supply.

App Note [2] Bias Arrangement -

For Parallel Stage Bias (Recommended for general applications) -- The same as Individual Stage Bias but all the drain or gate pad DC bypass capacitors (~100-200 pf) can be combined. Additional DC bypass capacitance (~0.01 uF) is also recommended to all DC or combination (if gate or drains are tied together) of DC bias pads.

For Individual Stage Bias (Recommended for saturated applications) -- Each DC pad (Vd1,2 and Vg1,2) needs to have DC bypass capacitance (~100-200 pf) as close to the device as possible. Additional DC bypass capacitance (~0.01 uF) is also recommended.

MTTF Tables

These numbers were calculated based on accelerated life test information and thermal model analysis received from the fabricating foundry.

Backplate Temperature	Channel Temperature	Rth	MTTF Hours	FITs
55 deg Celsius	83.0 deg Celsius	159.9° C/W	8.28E+10	1.21E-02
75 deg Celsius	105.1 deg Celsius	171.9° C/W	5.33E+09	1.88E-01
95 deg Celsius	127.0 deg Celsius	182.6° C/W	4.75E+08	2.11E+00

Bias Conditions: Vd1=Vd2=3.5V, Id1=25 mA, Id2=25 mA

Backplate Temperature	Channel Temperature	Rth	MTTF Hours	FITs
55 deg Celsius	149.1 deg Celsius	171.2° C/W	8.14E+07	1.23E+01
75 deg Celsius	175.4 deg Celsius	182.5° C/W	7.93E+06	1.26E+02
95 deg Celsius	201.0 deg Celsius	192.8° C/W	1.04E+06	9.63E+02


Bias Conditions: Vd1=Vd2=5.5V, Id1=50 mA, Id2=50mA

Mimix Broadband, Inc., 10795 Rockley Rd., Houston, Texas 77099 Tel: 281.988.4600 Fax: 281.988.4615 mimixbroadband.com

February 2008 - Rev 25-Feb-08



Device Schematic



February 2008 - Rev 25-Feb-08



Handling and Assembly Information

CAUTION! - Mimix Broadband MMIC Products contain gallium arsenide (GaAs) which can be hazardous to the human body and the environment. For safety, observe the following procedures:

- Do not ingest.
- Do not alter the form of this product into a gas, powder, or liquid through burning, crushing, or chemical processing as these by-products are dangerous to the human body if inhaled, ingested, or swallowed.
- Observe government laws and company regulations when discarding this product. This product must be discarded in accordance with methods specified by applicable hazardous waste procedures.

Life Support Policy - Mimix Broadband's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President and General Counsel of Mimix Broadband. As used herein: (1) Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user. (2) A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

ESD - Gallium Arsenide (GaAs) devices are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic containers, which should be opened in cleanroom conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickups or, with care, sharp tweezers.

Die Attachment - GaAs Products from Mimix Broadband are 0.100 mm (0.004") thick and have vias through to the backside to enable grounding to the circuit. Microstrip substrates should be brought as close to the die as possible. The mounting surface should be clean and flat. If using conductive epoxy, recommended epoxies are Tanaka TS3332LD, Die Mat DM6030HK or DM6030HK-Pt cured in a nitrogen atmosphere per manufacturer's cure schedule. Apply epoxy sparingly to avoid getting any on to the top surface of the die. An epoxy fillet should be visible around the total die periphery. For additional information please see the Mimix "Epoxy Specifications for Bare Die" application note. If eutectic mounting is preferred, then a fluxless gold-tin (AuSn) preform, approximately 0.001² thick, placed between the die and the attachment surface should be used. A die bonder that utilizes a heated collet and provides scrubbing action to ensure total wetting to prevent void formation in a nitrogen atmosphere is recommended. The gold-tin eutectic (80% Au 20% Sn) has a melting point of approximately 280 °C (Note: Gold Germanium should be avoided). The work station temperature should be 310 °C +/- 10 °C. Exposure to these extreme temperatures should be kept to minimum. The collet should be heated, and the die pre-heated to avoid excessive thermal shock. Avoidance of air bridges and force impact are critical during placement.

Wire Bonding - Windows in the surface passivation above the bond pads are provided to allow wire bonding to the die's gold bond pads. The recommended wire bonding procedure uses 0.076 mm x 0.013 mm (0.003" x 0.0005") 99.99% pure gold ribbon with 0.5-2% elongation to minimize RF port bond inductance. Gold 0.025 mm (0.001") diameter wedge or ball bonds are acceptable for DC Bias connections. Aluminum wire should be avoided. Thermo-compression bonding is recommended though thermosonic bonding may be used providing the ultrasonic content of the bond is minimized. Bond force, time and ultrasonics are all critical parameters. Bonds should be made from the bond pads on the die to the package or substrate. All bonds should be as short as possible.

Ordering Information

Part Number for Ordering XB1006-BD-000V XB1006-BD-000W XB1006-BD-EV1

Description

Where "V" is RoHS compliant die packed in vacuum release gel paks Where "W" is RoHS compliant die packed in waffle trays XB1006 die evaluation module



Proper ESD procedures should be followed when handling this device.

Mimix Broadband, Inc., 10795 Rockley Rd., Houston, Texas 77099 Tel: 281.988.4600 Fax: 281.988.4615 mimixbroadband.com Page 11 of 11