

4 mm Oval Precision Optical Performance LED Lamps

Data Sheet

SunPower Series

**Agilent HLMP-RG10, HLMP-SG10, HLMP-RL10, HLMP-SL10,
HLMP-RD11, HLMP-SD11, HLMP-RL11, HLMP-SL11,
HLMP-RM11, HLMP-SM11, HLMP-RB11, HLMP-SB11**

Description

These Precision Optical Performance Oval LEDs are specifically designed for Full Color/Video and Passenger Information signs. The oval shaped radiation pattern ($60^\circ \times 120^\circ$) and high luminous intensity ensure that these devices are excellent for wide field of view outdoor applications where a wide viewing angle and readability in sunlight are essential. These lamps have very smooth, matched radiation patterns ensuring consistent color mixing in full color applications, message uniformity across the viewing angle of the sign.

High efficiency LED materials are used in these lamps: Aluminum Indium Gallium Phosphide

(AlInGaP) for Red and Amber color and Indium Gallium Nitride (InGaN) for Blue and Green. There are two families of red and amber lamps, AlInGaP and the higher performance AlInGaP II. Each lamp is made with an advanced optical grade epoxy offering superior high temperature and high moisture resistance in outdoor applications. The package epoxy contains both uv-a and uv-b inhibitors to reduce the effects of long term exposure to direct sunlight.

Designers can select parallel (where the axis of the leads is parallel to the wide axis of the oval radiation pattern) or perpendicular orientation. Both lamps are available in tinted version.

Features

- Well defined spatial radiation pattern
- Viewing angle:
major axis 120°
minor axis 60°
- High luminous output
- Two red and amber intensity levels
AlInGaP (bright) and
AlInGaP II (brightest)
- Colors
626/630 nm red
590/592 nm amber
526 nm green
470 nm blue
- Superior resistance to moisture
- UV resistant epoxy

Benefits

- Viewing angle designed for wide field of view applications
- Superior performance for outdoor environments
- Radiation pattern matched for red, green, and blue for full color sign

Applications


- Full color signs

CAUTION: The Blue and Green LEDs are Class 1 ESD sensitive. Please observe appropriate precautions during handling and processing. Refer to Agilent Technologies Application Note AN-1142 for additional details.



Agilent Technologies

Package Dimensions



DIMENSIONS ARE IN MILLIMETERS (INCHES).

Device Selection Guide for AlInGaP

Part Number	Color and Dominant Wavelength λ_d (nm) Typ.	Luminous Intensity I _v (mcd) at 20 mA	Leads with Stand-Offs	Leadframe Orientation	Package Drawing
HLMP-SG10-GK000	Red 626	120 460	Yes	Perpendicular	A
HLMP-RG10-GK000	Red 626	120 460	Yes	Parallel	B
HLMP-SG10-JM000	Red 626	205 780	Yes	Perpendicular	A
HLMP-RG10-JM000	Red 626	205 780	Yes	Parallel	B
HLMP-SL10-FJ000	Amber 590	96 360	Yes	Perpendicular	A
HLMP-RL10-FJ000	Amber 590	96 360	Yes	Parallel	B
HLMP-SL10-HL000	Amber 590	155 600	Yes	Perpendicular	A
HLMP-RL10-HL000	Amber 590	155 600	Yes	Parallel	B
HLMP-SL10-LP000	Amber 590	345 1330	Yes	Perpendicular	A
HLMP-RL10-LP000	Amber 590	345 1330	Yes	Parallel	B

Notes:

1. The luminous intensity is measured on the mechanical axis of the lamp package.
2. The optical axis is closely aligned with the package mechanical axis.
3. The dominant wavelength, λ_d , is derived from the CIE Chromaticity Diagram and represents the color of the lamp.

Device Selection Guide for AlInGaP II

Part Number	Color and Dominant Wavelength λ_d (nm) Typ.	Luminous Intensity I_v (mcd) at 20 mA		Leads with Stand-Offs	Leadframe Orientation	Package Drawing
		Min.	Max.			
HLMP-SD11-LP000	Red 630	345	1330	Yes	Perpendicular	A
HLMP-RD11-LP000	Red 630	345	1330	Yes	Parallel	B
HLMP-SD11-LPT00	Red 630	345	1330	Yes	Perpendicular	A
HLMP-RD11-LPT00	Red 630	345	1330	Yes	Parallel	B
HLMP-SD11-MNT00	Red 630	450	1010	Yes	Perpendicular	A
HLMP-SL11-HLR00	Amber 592	155	600	Yes	Perpendicular	A
HLMP-SL11-LP000	Amber 592	345	1330	Yes	Perpendicular	A
HLMP-RL11-LP000	Amber 592	345	1330	Yes	Parallel	B
HLMP-SL11-LPR00	Amber 592	345	1330	Yes	Perpendicular	A
HLMP-RL11-LPR00	Amber 592	345	1330	Yes	Parallel	B
HLMP-SL11-LPV00	Amber 592	345	1330	Yes	Perpendicular	A
HLMP-RL11-LPV00	Amber 592	345	1330	Yes	Parallel	B

Notes:

1. The luminous intensity is measured on the mechanical axis of the lamp package.
2. The optical axis is closely aligned with the package mechanical axis.
3. The dominant wavelength, λ_d , is derived from the CIE Chromaticity Diagram and represents the color of the lamp.

Device Selection Guide for InGaN

Part Number	Color and Dominant Wavelength λ_d (nm) Typ.	Luminous Intensity I_v (mcd) at 20 mA		Leads with Stand-Offs	Leadframe Orientation	Package Drawing
		Min.	Max.			
HLMP-SM11-LP000	Green 526	345	1330	Yes	Perpendicular	A
HLMP-RM11-LP000	Green 526	345	1330	Yes	Parallel	B
HLMP-SB11-EH000	Blue 470	70	270	Yes	Perpendicular	A
HLMP-RB11-EH000	Blue 470	70	270	Yes	Parallel	B

Notes:

4. The luminous intensity is measured on the mechanical axis of the lamp package.
5. The optical axis is closely aligned with the package mechanical axis.
6. The dominant wavelength, λ_d , is derived from the CIE Chromaticity Diagram and represents the color of the lamp.

Part Numbering System

HLMP - x x xx - x x x xx

Mechanical Options

- 00: Bulk Packaging
- DD: Ammo Pack
- YY: Flexi-Bin; Bulk Packaging
- ZZ: Flexi-Bin; Ammo Pack

Color Bin & VF Selections

- O: No Color Bin Limitation
- R: Amber Color Bins 1, 2, 4, and 6 with VF Maximum of 2.6 V
- T: Red Color with VF Maximum of 2.6 V
- V: Amber Color Bins 1, 2, 4, and 6 with VF Maximum of 2.6 V

Maximum Intensity Bin

- O: No Iv Bin Limitation

Minimum Intensity Bin

Refer to Device Selection Guide

Color

- B: 470 nm Blue
- D: 630 nm Red
- G: 626 nm Red
- L: 590/592 nm Amber
- M: 526 nm Green

Package

- R: 4 mm 60° x 120° Oval, Parallel
- S: 4 mm 60° x 120° Oval, Perpendicular

Absolute Maximum Ratings

T_A = 25°C

Parameter	Blue and Green	Amber and Red
DC Forward Current ^[1]	30 mA	50 mA
Peak Pulsed Forward Current	100 mA	100 mA
Average Forward Current	30 mA	30 mA
Reverse Voltage (I _R = 100 µA)	5 V	5 V
Power Dissipation	120 mW	120 mW
LED Junction Temperature	130°C	130°C
Operating Temperature Range	-40°C to +80°C	-40°C to +100°C
Storage Temperature Range	-40°C to +100°C	-40°C to +120°C
Soldering Temperature	260° for 5 sec	260° for 5 sec

Note:

1. Derate linearly as shown in Figures 6 and 7.

Electrical/Optical Characteristics

$T_A = 25^\circ\text{C}$

Parameter	Symbol	Min.	Typ.	Max.	Units	Test Conditions
Typical Viewing Angle ^[1]	$2\theta_{1/2}$				deg	
Major			120			
Minor			60			
Forward Voltage	V_F				V	$I_F = 20 \text{ mA}$
Red ($\lambda_d = 626 \text{ nm}$)		1.9	2.4			
Red ($\lambda_d = 630 \text{ nm}$)		2.0	2.4 ^[2]			
Amber ($\lambda_d = 590 \text{ nm}$)		2.02	2.4			
Amber ($\lambda_d = 592 \text{ nm}$)		2.15	2.4 ^[2]			
Blue ($\lambda_d = 470 \text{ nm}$)		3.5	4.0			
Green ($\lambda_d = 526 \text{ nm}$)		3.5	4.0			
Reverse Voltage	V_R				V	$I_R = 100 \mu\text{A}$
Amber and Red		5	20			
Blue and Green		5	—			
Peak Wavelength	λ_{PEAK}				nm	Peak of Wavelength of Spectral Distribution at $I_F = 20 \text{ mA}$
Red ($\lambda_d = 626 \text{ nm}$)		635				
Red ($\lambda_d = 630 \text{ nm}$)		639				
Amber ($\lambda_d = 590 \text{ nm}$)		592				
Amber ($\lambda_d = 592 \text{ nm}$)		594				

LED Indicators

Parameter	Symbol	Min.	Typ.	Max.	Units	Test Conditions
Blue ($\lambda_d = 470 \text{ nm}$)		467				
Green ($\lambda_d = 526 \text{ nm}$)		524				
Spectral Halfwidth	$\Delta\lambda_{1/2}$				nm	Wavelength Width at Spectral Distribution $1/2$ Power Point at $I_F = 20 \text{ mA}$
Red ($\lambda_d = 626/630 \text{ nm}$)		17				
Amber ($\lambda_d = 590/592 \text{ nm}$)		17				
Blue ($\lambda_d = 470 \text{ nm}$)		20				
Green ($\lambda_d = 526 \text{ nm}$)		35				
Capacitance	C				pF	$V_F = 0, F = 1 \text{ MHz}$
All Colors		40				
Thermal Resistance	$R\theta_{J-\text{PIN}}$				°C/W	LED Junction-to-Cathode Lead
All Colors		240				
Luminous Efficacy ^[3]	η_v				lm/W	Emitted Luminous Power/Emitted Radiant Power
Red ($\lambda_d = 626 \text{ nm}$)		150				
Red ($\lambda_d = 630 \text{ nm}$)		155				
Amber ($\lambda_d = 590 \text{ nm}$)		480				
Amber ($\lambda_d = 592 \text{ nm}$)		500				
Blue ($\lambda_d = 470 \text{ nm}$)		70				
Green ($\lambda_d = 526 \text{ nm}$)		540				

Notes:

1. $2\theta_{1/2}$ is the off-axis angle where the luminous intensity is the on-axis intensity.
2. For options -xxRxx, -xxTxx, and -xxVxx, maximum forward voltage, V_F , is 2.6 V.
3. The radiant intensity, I_e , in watts per steradian, may be found from the equation $I_e = I_v/\eta_v$, where I_v is the luminous intensity in candelas and η_v is the luminous efficacy in lumens/watt.




Figure 1. Relative intensity vs. wavelength.




Figure 2. Amber, Red forward current vs. forward voltage.




Figure 3. Blue, Green forward current vs. forward voltage.




Figure 4. Amber, Red relative luminous intensity vs. forward current.




Figure 5. Blue, Green relative luminous intensity vs. forward current.




Figure 6. Amber, Red maximum forward current vs. ambient temperature.




Figure 7. Blue, Green maximum forward current vs. ambient temperature.




Figure 8a. Representative spatial radiation pattern for major axis.

Intensity Bin Limits
(mcd at 20 mA)

Bin Name	Min.	Max.
E	85	110
F	110	140
G	140	180
H	180	240
J	240	310
K	310	400
L	400	520
M	520	680
N	680	880
P	880	1150

Tolerance for each bin limit is $\pm 15\%$.

Note:

1. Bin categories are established for classification of products. Products may not be available in all bin categories.




Figure 8b. Representative spatial radiation pattern for minor axis.

Color Bin Limits (nm at 20 mA)

Blue	Color Range (nm)	
Bin	Min.	Max.
1	460.0	464.0
2	464.0	468.0
3	468.0	472.0
4	472.0	476.0
5	476.0	480.0

Tolerance for each bin limit is ± 2 nm.

Amber	Color Range (nm)	
Bin ID	Min.	Max.
1	584.5	587.0
2	587.0	589.5
4	589.5	592.0
6	592.0	594.5

Tolerance for each bin limit is ± 0.5 nm.

Green	Color Range (nm)	
Bin ID	Min.	Max.
1	520.0	524.0
2	524.0	528.0
3	528.0	532.0
4	532.0	536.0
5	536.0	540.0

Tolerance for each bin limit is ± 0.5 nm.

Note:

1. All bin categories are established for classification of products. Products may not be available in all bin categories. Please contact your Agilent representatives for further information.

www.agilent.com/semiconductors

For product information and a complete list of distributors, please go to our web site.

For technical assistance call:

Americas/Canada: +1 (800) 235-0312 or (408) 654-8675

Europe: +49 (0) 6441 92460

China: 10800 650 0017

Hong Kong: (+65) 6271 2451

India, Australia, New Zealand: (+65) 6271 2394

Japan: (+81 3) 3335-8152(Domestic/International), or 0120-61-1280(Domestic Only)

Korea: (+65) 6271 2194

Malaysia, Singapore: (+65) 6271 2054

Taiwan: (+65) 6271 2654

Data subject to change.

Copyright © 2002 Agilent Technologies, Inc.

Obsoletes 5988-7318EN

October 29, 2002

5988-8250EN



Agilent Technologies